

[All Products](#) / [Lights and Illumination](#) / [Machine Vision Lighting](#) / [Ring Lights](#)

Advanced Illumination High Intensity Ring Lights See More by [Advanced Illumination](#)



- Slim Profile to Ease System Integration
- High Brightness LEDs
- Multiple Size, Wavelength, and Working Distance Options

Common Specifications

General

LED Lifetime (hours):	50,000	Number of Channels:	1.00
Type of Illumination:	LED Illuminator	Note:	Optional Manual Intensity Adjustment #86-887 and #89-555 are Available
Manufacturer:	Advanced Illumination	Geometry:	Ring Light
Illumination Mode:	Constant		

Hardware & Interface Connectivity

Connector:	Flying Leads
Power Supply:	Power Supply Required and Sold Separately: USA: #66-855 Europe: #66-855 Japan: #89-513 Korea: #33-773 China: #66-855

Environmental & Durability Factors

Operating Temperature (°C):	0 to 60
------------------------------------	---------

Technical Information

Products

Color	Wavelength (nm)	Dia. (mm)	Illumination Mode	Inner Diameter (mm)	Outer Diameter (mm)	Stock Number	Price	Buy
White	-	74.90	Constant	M35.5 x 0.5	74.9	#88-484	£378.25	2 In Stock
Blue	470.00	74.90	Constant	M35.5 x 0.5	74.9	#88-485	£378.25	Contact Us
Red	625.00	74.90	Constant	M35.5 x 0.5	74.9	#88-486	£378.25	Contact Us
White	-	116.80	Constant	M67 x 0.75	116.8	#88-487	£731.00	1 In Stock
Blue	470.00	116.80	Constant	M67 x 0.75	116.8	#88-488	£731.00	Contact Us
Red	625.00	116.80	Constant	M67 x 0.75	116.8	#88-489	£731.00	Contact Us
White	-	152.40	Constant	66.00	152.4	#88-490	£1,181.50	Contact Us
Blue	470.00	152.40	Constant	66.00	152.4	#88-491	£1,224.00	Contact Us
Red	625.00	152.40	Constant	66.00	152.4	#88-492	£1,181.50	1 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
 Phone: 1-800-363-1992 :
www.edmundoptics.com