

TECHSPEC®

Convex Mirrors



- Precision Polished Surface
- $\lambda/2$ Surface Accuracy
- Variety of Coating Options Offered

Common Specifications

Physical & Mechanical Properties			
Clear Aperture (%):	90.00	Dimensional Tolerance (mm):	+0.0/-0.1
Thickness Tolerance (mm):	±0.1		
Optical Properties			
Coating Type:	Metal		
Focal Length Tolerance (%):	±2	Substrate:	N-BK7
Surface Accuracy:	$\lambda/2$	Surface Quality:	60-40

Technical Information

Products

Dia. (mm)	FL (mm)	Coating	Coating Specification	Surface Accuracy	Wavelength Range (nm)	Stock Number	Price	Buy
25.00	-12.50	Enhanced Aluminum (450-650nm)	R _{avg} >95% @ 450 - 650nm	λ/2	450 - 650	#87-666	£46.84 Volume Pricing	Contact Us
25.00	-12.50	Protected Aluminum (400-700nm)	R _{avg} >85% @ 400 - 700nm	λ/2	400 - 700	#87-655	£43.33 Volume Pricing	14 In Stock
25.00	-12.50	Protected Gold (700-10000nm)	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	λ/2	700 - 2000	#87-688	£56.46 Volume Pricing	Contact Us
25.00	-12.50	Protected Silver (450-10000nm)	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	λ/2	500 - 10000	#87-677	£52.09 Volume Pricing	Contact Us
25.00	-25.00	Enhanced Aluminum (450-650nm)	R _{avg} >95% @ 450 - 650nm	λ/2	450 - 650	#87-667	£46.84 Volume Pricing	2 In Stock
25.00	-25.00	Protected Aluminum (400-700nm)	R _{avg} >85% @ 400 - 700nm	λ/2	400 - 700	#87-656	£43.33 Volume Pricing	Contact Us
25.00	-25.00	Protected Gold (700-10000nm)	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	λ/2	700 - 2000	#87-689	£56.46 Volume Pricing	3 In Stock
25.00	-25.00	Protected Silver (450-10000nm)	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	λ/2	500 - 10000	#87-678	£52.09 Volume Pricing	Contact Us
25.00	-50.00	Enhanced Aluminum (450-650nm)	R _{avg} >95% @ 450 - 650nm	λ/2	450 - 650	#87-668	£46.84 Volume Pricing	3 In Stock
25.00	-50.00	Protected Aluminum (400-700nm)	R _{avg} >85% @ 400 - 700nm	λ/2	400 - 700	#87-657	£43.33 Volume Pricing	6 In Stock

25.00	-50.00	Protected Gold (700-10000nm)	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	λ/2	700 - 2000	#87-690	£56.46 Volume Pricing	4 In Stock
25.00	-50.00	Protected Silver (450-10000nm)	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	λ/2	500 - 10000	#87-679	£52.09 Volume Pricing	Contact Us
25.00	-100.00	Enhanced Aluminum (450-650nm)	R _{avg} >95% @ 450 - 650nm	λ/2	450 - 650	#87-669	£46.84 Volume Pricing	4 In Stock
25.00	-100.00	Protected Aluminum (400-700nm)	R _{avg} >85% @ 400 - 700nm	λ/2	400 - 700	#87-658	£43.33 Volume Pricing	2 In Stock
25.00	-100.00	Protected Gold (700-10000nm)	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	λ/2	700 - 2000	#87-691	£56.46 Volume Pricing	Contact Us
25.00	-100.00	Protected Silver (450-10000nm)	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	λ/2	500 - 10000	#87-680	£52.09 Volume Pricing	5 In Stock
25.00	-150.00	Enhanced Aluminum (450-650nm)	R _{avg} >95% @ 450 - 650nm	λ/2	450 - 650	#87-670	£46.84 Volume Pricing	3 In Stock
25.00	-150.00	Protected Aluminum (400-700nm)	R _{avg} >85% @ 400 - 700nm	λ/2	400 - 700	#87-659	£43.33 Volume Pricing	Contact Us
25.00	-150.00	Protected Gold (700-10000nm)	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	λ/2	700 - 2000	#87-692	£56.46 Volume Pricing	1 In Stock
25.00	-150.00	Protected Silver (450-10000nm)	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	λ/2	500 - 10000	#87-681	£52.09 Volume Pricing	Contact Us
25.00	-200.00	Enhanced Aluminum (450-650nm)	R _{avg} >95% @ 450 - 650nm	λ/2	450 - 650	#87-671	£46.84 Volume Pricing	1 In Stock

25.00	- 200.00	Protected Aluminum (400- 700nm)	R _{avg} >85% @ 400 - 700nm	λ/2	400 - 700	#87-660	£43.33 Volume Pricing	2 In Stock
25.00	- 200.00	Protected Gold (700- 10000nm)	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	λ/2	700 - 2000	#87-693	£56.46 Volume Pricing	3 In Stock
25.00	- 200.00	Protected Silver (450- 10000nm)	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	λ/2	500 - 10000	#87-682	£52.09 Volume Pricing	Contact Us
50.00	-25.00	Enhanced Aluminum (450- 650nm)	R _{avg} >95% @ 450 - 650nm	λ/2	450 - 650	#87-672	£64.35 Volume Pricing	2 In Stock
50.00	-25.00	Protected Aluminum (400- 700nm)	R _{avg} >85% @ 400 - 700nm	λ/2	400 - 700	#87-661	£57.34 Volume Pricing	5 In Stock
50.00	-25.00	Protected Gold (700- 10000nm)	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	λ/2	700 - 2000	#87-694	£83.17 Volume Pricing	Contact Us
50.00	-25.00	Protected Silver (450- 10000nm)	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	λ/2	500 - 10000	#87-683	£70.04 Volume Pricing	Contact Us
50.00	-50.00	Enhanced Aluminum (450- 650nm)	R _{avg} >95% @ 450 - 650nm	λ/2	450 - 650	#87-673	£64.35 Volume Pricing	Contact Us
50.00	-50.00	Protected Aluminum (400- 700nm)	R _{avg} >85% @ 400 - 700nm	λ/2	400 - 700	#87-662	£57.34 Volume Pricing	5 In Stock
50.00	-50.00	Protected Gold (700- 10000nm)	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	λ/2	700 - 2000	#87-695	£83.17 Volume Pricing	5 In Stock
50.00	-50.00	Protected Silver (450- 10000nm)	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	λ/2	500 - 10000	#87-684	£70.04 Volume Pricing	Contact Us

50.00	- 100.00	Enhanced Aluminum (450-650nm)	R _{avg} >95% @ 450 - 650nm	λ/2	450 - 650	#87-674	£64.35 Volume Pricing	7 In Stock
50.00	- 100.00	Protected Aluminum (400-700nm)	R _{avg} >85% @ 400 - 700nm	λ/2	400 - 700	#87-663	£57.34 Volume Pricing	Contact Us
50.00	- 100.00	Protected Gold (700-10000nm)	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	λ/2	700 - 2000	#87-696	£83.17 Volume Pricing	Contact Us
50.00	- 100.00	Protected Silver (450-10000nm)	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	λ/2	500 - 10000	#87-685	£70.04 Volume Pricing	1 In Stock
50.00	- 200.00	Enhanced Aluminum (450-650nm)	R _{avg} >95% @ 450 - 650nm	λ/2	450 - 650	#87-675	£64.35 Volume Pricing	Contact Us
50.00	- 200.00	Protected Aluminum (400-700nm)	R _{avg} >85% @ 400 - 700nm	λ/2	400 - 700	#87-664	£57.34 Volume Pricing	5 In Stock
50.00	- 200.00	Protected Gold (700-10000nm)	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	λ/2	700 - 2000	#87-697	£83.17 Volume Pricing	2 In Stock
50.00	- 200.00	Protected Silver (450-10000nm)	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	λ/2	500 - 10000	#87-686	£70.04 Volume Pricing	1 In Stock
50.00	- 400.00	Enhanced Aluminum (450-650nm)	R _{avg} >95% @ 450 - 650nm	λ/2	450 - 650	#87-676	£64.35 Volume Pricing	9 In Stock
50.00	- 400.00	Protected Aluminum (400-700nm)	R _{avg} >85% @ 400 - 700nm	λ/2	400 - 700	#87-665	£57.34 Volume Pricing	Contact Us
50.00	- 400.00	Protected Gold (700-10000nm)	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	λ/2	700 - 2000	#87-698	£83.17 Volume Pricing	1 In Stock

50.00	-	Protected Silver (450-10000nm)	R _{avg} >98% @ 450 - 2000nm	λ/2	500 - 10000	#87-687	£70.04 Volume Pricing	3 In Stock
400.00			R _{avg} >98% @ 2000 - 10,000nm					



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com