

[All Products](#) / [Lights and Illumination](#) / [Machine Vision Lighting](#) / [Bar Lights](#)

Advanced Illumination EuroBrite™ Bar Lights [See More by Advanced Illumination](#)



- Daisy Chain up to Four Units
- Requires No Heat Sink
- Available in White, Red, and Blue

Common Specifications

General			
Operating Lifetime (hours):	50,000	Type of Illumination:	LED Illuminator
Note:	See Technical Information Tab for Typical Intensity	Manufacturer:	Advanced Illumination
Geometry:	Bar Light	Illumination Mode:	Strobed or Constant
Physical & Mechanical Properties			
Dimensions (mm):	300 x 64 x 30	Weight (g):	241.00
Electrical			
Maximum Input Current:	0.42 - 0.49A	Analog Intensity Control:	10% @ 0.7V, 100% @ 10V
Trigger-to-Pulse Latency:	10µm		
Hardware & Interface Connectivity			
Connector:	Flying Leads		
Input Voltage (V):	24V nominal (min. 22 / max. 28)	Power Supply:	Power Supply Required and Sold Separately: USA: #66-855 Europe: #66-855 Japan: #89-513 Korea: #33-773 China: #66-855
Environmental & Durability Factors			
Operating Temperature (°C):	0 - 60	Environmental Rating:	IP67

Technical Information

Products

Dimensions (mm)	Color	Wavelength (nm)	Stock Number	Price	Buy
300 x 64 x 30	White	-	#33-444	£331.50	1 In Stock
300 x 64 x 30	Red	625.00	#33-445	£331.50	Contact Us
300 x 64 x 30	Blue	470.00	#33-446	£637.50	Contact Us



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com