

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Plano-Convex \(PCX\) Lenses](#) / [Fused Silica Plano-Convex \(PCX\) Lenses](#)

TECHSPEC®

633nm Laser Line Coated Fused Silica PCX Lenses



- <0.25% Reflection at 633nm for HeNe Applications
- 5 - 50mm Diameters Available
- 10 - 250mm EFL Designs Available
- [405nm](#), [532nm](#), [1064nm](#), and [1550nm](#) V-Coated Options Offered

Common Specifications

Physical & Mechanical Properties

Bevel:	Protective as needed
--------	----------------------

Optical Properties

Surface Quality:	40-20
------------------	-------

Power (P-V) @ 632.8nm:	1.5λ
------------------------	------

Irregularity (P-V) @ 632.8nm:	λ/4
-------------------------------	-----

Focal Length Tolerance (%):	±1
-----------------------------	----

Design Wavelength DWL (nm):	633
-----------------------------	-----

Technical Information

Products

Dia. (mm)	EFL (mm)	BFL (mm)	Coating	Substrate	Stock Number	Price	Buy
5.00	10.00	8.63	Laser V-Coat (633nm)	Fused Silica	#34-106	£120.82 Volume Pricing	4 In Stock
5.00	15.00	13.83	Laser V-Coat (633nm)	Fused Silica	#34-107	£113.82 Volume Pricing	5 In Stock
5.00	20.00	18.97	Laser V-Coat (633nm)	Fused Silica	#34-108	£113.82 Volume Pricing	4 In Stock
5.00	25.00	23.97	Laser V-Coat (633nm)	Fused Silica	#34-109	£113.82 Volume Pricing	5 In Stock
6.00	12.00	10.63	633nm V-Coat	Fused Silica (Corning 7980)	#25-871	£119.94 Volume Pricing	8 In Stock
6.00	21.00	19.63	633nm V-Coat	Fused Silica (Corning 7980)	#25-872	£115.57 Volume Pricing	5 In Stock
6.00	24.00	22.63	633nm V-Coat	Fused Silica (Corning 7980)	#25-873	£115.57 Volume Pricing	4 In Stock
6.00	36.00	34.63	633nm V-Coat	Fused Silica (Corning 7980)	#25-874	£115.57 Volume Pricing	9 In Stock
9.00	12.00	9.26	633nm V-Coat	Fused Silica (Corning 7980)	#25-875	£122.57 Volume Pricing	5 In Stock
9.00	18.00	15.94	633nm V-Coat	Fused Silica (Corning 7980)	#25-876	£122.57 Volume Pricing	9 In Stock
9.00	27.00	25.63	633nm V-Coat	Fused Silica (Corning 7980)	#25-877	£118.19 Volume Pricing	5 In Stock
9.00	36.00	34.63	633nm V-Coat	Fused Silica (Corning 7980)	#25-878	£118.19 Volume Pricing	5 In Stock

12.00	18.00	15.26	Laser V-Coat (633nm)	Fused Silica	#34-110	£127.82 Volume Pricing	Contact Us
12.00	25.00	22.31	Laser V-Coat (633nm)	Fused Silica	#34-111	£127.82 Volume Pricing	4 In Stock
12.00	30.00	27.56	Laser V-Coat (633nm)	Fused Silica	#34-112	£123.45 Volume Pricing	2 In Stock
12.00	36.00	34.29	Laser V-Coat (633nm)	Fused Silica	#34-113	£123.45 Volume Pricing	3 In Stock
12.00	50.00	48.01	Laser V-Coat (633nm)	Fused Silica	#34-114	£116.44 Volume Pricing	Contact Us
12.00	100.00	98.33	Laser V-Coat (633nm)	Fused Silica	#34-115	£116.44 Volume Pricing	5 In Stock
25.00	38.00	33.03	Laser V-Coat (633nm)	Fused Silica	#34-116	£144.46 Volume Pricing	14 In Stock
25.00	50.00	46.00	Laser V-Coat (633nm)	Fused Silica	#34-117	£144.46 Volume Pricing	2 In Stock
25.00	60.00	56.92	Laser V-Coat (633nm)	Fused Silica	#34-118	£140.08 Volume Pricing	2 In Stock
25.00	75.00	71.96	Laser V-Coat (633nm)	Fused Silica	#34-119	£140.08 Volume Pricing	2 In Stock
25.00	100.00	97.40	Laser V-Coat (633nm)	Fused Silica	#34-120	£140.08 Volume Pricing	5 In Stock
50.00	100.00	93.84	Laser V-Coat (633nm)	Fused Silica	#34-125	£270.53 Volume Pricing	4 In Stock
25.00	125.00	122.65	Laser V-Coat (633nm)	Fused Silica	#34-121	£133.08 Volume Pricing	16 In Stock
25.00	150.00	147.86	Laser V-Coat (633nm)	Fused Silica	#34-122	£133.08 Volume Pricing	14 In Stock

25.00	200.00	198.02	Laser V-Coat (633nm)	Fused Silica	#34-123	£133.08 Volume Pricing	5 In Stock
50.00	75.00	66.43	Laser V-Coat (633nm)	Fused Silica	#34-124	£270.53 Volume Pricing	5 In Stock
50.00	150.00	145.20	Laser V-Coat (633nm)	Fused Silica	#34-126	£266.15 Volume Pricing	5 In Stock
50.00	200.00	195.19	Laser V-Coat (633nm)	Fused Silica	#34-127	£266.15 Volume Pricing	2 In Stock
50.00	250.00	245.21	Laser V-Coat (633nm)	Fused Silica	#34-128	£266.15 Volume Pricing	5 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com