

[All Products](#) / [Imaging Lenses](#) / [M12 Lenses \(S-Mount Lenses\)](#)

TECHSPEC® Liquid Lens M12 Lenses



- Up to 1/1.8", S-Mount Lens
- Up to 5 MegaPixels, 2.8µm Pixel Size Sensors
- Liquid Lens Provides Quick Autofocus
- 6mm to 16mm Focal Length

Common Specifications

General

Series: LL M12 Series		Note: Separate driver not included. Electronic development kit #28-773 recommended. When using a Maxim driver board (#12-247, #12-248, or #17-172) the jumper at ST2 must be removed before use to ensure optimal performance and product lifetime. Watch this video for more information.	
Integrated Liquid Lens Model:	Corning® Varioptic® A-39N0	IR Cut Filter:	No

Physical & Mechanical Properties

Iris Option:	Fixed	Flange Distance (mm):	14.025
---------------------	-------	------------------------------	--------

Optical Properties

Wavelength Range (nm):	400 - 700	Aperture (f/#):	f/2.4
Coating Specification:	$\lambda/4$ MgF ₂ @ 550nm		

Sensor

Pixel Size (μm):	2.74
-------------------------	------

Threading & Mounting

Filter Thread:	N/A	Mount:	S-Mount (M12 x 0.5)
-----------------------	-----	---------------	---------------------

Technical Information

Products

FL (mm)	Aperture (f/#)	Max. Sensor Format	WD (mm)	IR Cut Filter	Stock Number	Price	Buy
6.00	f/2.4	1/2"	100 - ∞	No	#37-521	£374.00	2 In Stock
8.00	f/2.4	1/2"	150 - ∞	No	#37-522	£374.00	Contact Us
12.00	f/2.4	1/2"	150 - ∞	No	#37-523	£374.00	Contact Us
16.00	f/2.4	1/1.8"	220 - ∞	No	#37-524	£374.00	Contact Us



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com