

[All Products](#) / [Lasers](#) / [Laser Mechanics](#)

# Acktar Blackened Laser Beam Traps and Blocks See More by [Acktar](#)



- Coated for High Absorbance of Laser Light
- Tubular Beam Trap or Thin, Flat Beam Block Designs
- M6 Tapped Hole for Easy Post Mounting

## Common Specifications

### Physical & Mechanical Properties

Construction:	Black Anodized Aluminum
---------------	-------------------------

### Optical Properties

Wavelength Range (nm):	100 - 10000
------------------------	-------------

### Electrical

Maximum Incident Power Density (W/cm <sup>2</sup> ):	20
--	----

### Threading & Mounting

Mounting Threads:	M6 x 1.0
-------------------	----------

## Technical Information

## Products

Title	Stock Number	Price	Buy
30mm Aperture, Acktar Blackened Laser Beam Trap	<a href="#">#13-515</a>	£224.02 <a href="#">Volume Pricing</a>	20+ In Stock
51mm Aperture, Acktar Blackened Laser Beam Trap	<a href="#">#13-516</a>	£293.63 <a href="#">Volume Pricing</a>	20+ In Stock
92 x 81mm Aperture, Acktar Blackened Laser Beam Block	<a href="#">#13-517</a>	£293.63 <a href="#">Volume Pricing</a>	Contact Us



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK  
Phone: 1-800-363-1992 :  
[www.edmundoptics.com](http://www.edmundoptics.com)