

[All Products](#) / [Optics](#) / [Optical Filters](#) / [Neutral Density \(ND\) Filters](#)

C-Mount Absorptive Neutral Density (ND) Filters



- Pre-mounted in Engraved C-Mount Housings
- Simplify Integration into Optical Systems
- Optical Densities from 0.15 to 2.5
- Also Available [Unmounted](#)

Common Specifications

Physical & Mechanical Properties

Clear Aperture CA (mm):	22.0	Parallelism (mm):	<0.02
Total Length (mm):	20.3		

Optical Properties

Substrate:	ND Filter Glass		
Coating:	Uncoated	Surface Quality:	80-50
Blocking Wavelength Range (nm):	400 - 700		

Threading & Mounting

Thread Type:	C-Mount		
Mount Diameter (mm):	30.0	Mount Included:	#56-353

Technical Information

Products

CA (mm)	Optical Density OD (Average)	Transmission (%)	Stock Number	Price	Buy
22.0	0.15	70	#13-015	£80.55 Volume Pricing	3 In Stock
22.0	0.2	63	#13-016	£80.55 Volume Pricing	4 In Stock
22.0	0.3	50	#13-017	£80.55 Volume Pricing	2 In Stock
22.0	0.4	40	#13-018	£80.55 Volume Pricing	2 In Stock
22.0	0.5	32	#13-019	£80.55 Volume Pricing	2 In Stock
22.0	0.6	25	#13-020	£80.55 Volume Pricing	2 In Stock
22.0	1.0	10	#13-021	£80.55 Volume Pricing	5 In Stock
22.0	1.3	5	#13-022	£80.55 Volume Pricing	12 In Stock
22.0	1.5	3	#13-023	£80.55 Volume Pricing	5 In Stock
22.0	2.0	1	#13-024	£80.55 Volume Pricing	5 In Stock
22.0	2.5	0.3	#13-025	£80.55 Volume Pricing	2 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com