

[All Products](#) / [Optics](#) / [Optical Filters](#) / [Longpass Filters](#)

C-Mount Longpass Glass Color Filters



- Pre-Mounted in Engraved C-Mount Housings
- Simplify Integration into Optical Systems
- SCHOTT or Hoya Color Glass Filters Available
- Also Available [Unmounted](#)

Common Specifications

Physical & Mechanical Properties

Clear Aperture CA (mm):	22.0	Total Length (mm):	20.3
-------------------------	------	--------------------	------

Optical Properties

Substrate:	Colored Glass	Coating:	Uncoated
Surface Quality:	80-50		

Threading & Mounting

Thread Type:	C-Mount		
Mount Diameter (mm):	30.0	Mount Included:	#56-353

Technical Information

Products

CA (mm)	Glass/Filter Number	Cut-On Wavelength (nm)	Mount Dia. (mm)	Thread Type	Stock Number	Price	Buy
22.0	SCHOTT WG320	320.00	30.0	C-Mount	#13-026	£84.92 Volume Pricing	2 In Stock
22.0	SCHOTT GG420	420.00	30.0	C-Mount	#13-027	£84.92 Volume Pricing	1 In Stock
22.0	SCHOTT GG495	495.00	30.0	C-Mount	#13-028	£84.92 Volume Pricing	3 In Stock
22.0	SCHOTT OG530	530.00	30.0	C-Mount	#13-029	£84.92 Volume Pricing	1 In Stock
22.0	SCHOTT OG550	550.00	30.0	C-Mount	#13-030	£84.92 Volume Pricing	3 In Stock
22.0	SCHOTT OG590	590.00	30.0	C-Mount	#13-031	£84.92 Volume Pricing	1 In Stock
22.0	Hoya R60	600.00	30.0	C-Mount	#13-032	£84.92 Volume Pricing	3 In Stock
22.0	SCHOTT RG630	630.00	30.0	C-Mount	#13-033	£84.92 Volume Pricing	2 In Stock
22.0	SCHOTT RG665	665.00	30.0	C-Mount	#13-034	£84.92 Volume Pricing	2 In Stock
22.0	SCHOTT RG695	695.00	30.0	C-Mount	#13-035	£84.92 Volume Pricing	1 In Stock
22.0	SCHOTT RG715	715.00	30.0	C-Mount	#13-036	£84.92 Volume Pricing	3 In Stock
22.0	SCHOTT RG780	780.00	30.0	C-Mount	#13-037	£84.92 Volume Pricing	4 In Stock
22.0	SCHOTT RG850	850.00	30.0	C-Mount	#13-038	£84.92 Volume Pricing	4 In Stock
22.0	SCHOTT RG1000	1,000.00	30.0	C-Mount	#13-039	£84.92 Volume Pricing	4 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com