

[All Products](#) / [Imaging Lenses](#) / [Cinema Production and Advanced Photography](#)

MikroMak™ Prime Probe Lenses



- Designed for Use from Macro to Infinity
- Ideal for Industrial and Cinema Production Applications
- Excellent Sharpness Over Depth of Field
- [MikroMak™ PetzVex™ Prime Probe Lenses](#) Also Available

Common Specifications

Physical & Mechanical Properties

Maximum Diameter (mm):	48.00
------------------------	-------

Optical Properties

Maximum Image Circle (mm):	43.30
----------------------------	-------

Sensor

Maximum Sensor Format:	35mm (43.3mm Image Circle)
------------------------	----------------------------

Threading & Mounting

Mount:	M42 x 0.75 (T-Mount)
--------	----------------------

Technical Information

Products

Title	Stock Number	Price	Buy
40mm MikroMak™ CINE Prime Probe Lens	#17-655	£3,026.00	1 In Stock
50mm MikroMak™ CINE Prime Probe Lens	#17-656	£3,026.00	1 In Stock
70mm MikroMak™ CINE Prime Probe Lens	#17-657	£2,494.75	1 In Stock
90mm MikroMak™ CINE Prime Probe Lens	#17-658	£2,494.75	1 In Stock
125mm MikroMak™ CINE Prime Probe Lens	#17-659	£2,494.75	1 In Stock
40mm MikroMak™ Prime Probe Lens	#16-133	£2,783.75	1 In Stock
50mm MikroMak™ Prime Probe Lens	#16-132	£2,783.75	1 In Stock
70mm MikroMak™ Prime Probe Lens	#16-131	£2,367.25	1 In Stock
90mm MikroMak™ Prime Probe Lens	#16-130	£2,367.25	1 In Stock
125mm MikroMak™ Prime Probe Lens	#16-129	£2,367.25	2 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com