

[All Products](#) / [Laser Optics](#) / [Laser Mirrors](#) / [Laser Line Mirrors](#)

Nd:YAG Laser Replacement Parts



- Output Couplers, Laser Line Mirrors, and Nd:YAG Rods
- 80% or 90% Reflectivity @ 1064nm Output Couplers
- 0.6% Nd Dopant Nd:YAG Rods
- Large Selection of Complementary [Nd:YAG Laser Optics](#) Available

Common Specifications

Optical Properties

Angle of Incidence (°):

0

Technical Information

Products

Title	Stock Number	Price	Buy
19.05mm Dia. 1064nm 0°, Nd:YAG Laser Line Mirror	#17-624	£127.82 Volume Pricing	1 In Stock
1064nm, 80R/20T, 19.05mm Dia., Nd:YAG Laser Output Coupler	#17-623	£136.58 Volume Pricing	20+ In Stock
1064nm, 90R/10T, 19.05mm Dia., Nd:YAG Laser Output Coupler	#17-622	£136.58 Volume Pricing	Contact Us
4mm Dia. x 79mm Length, 0.6% Dopant, Nd:YAG Laser Rod	#17-625	£516.55 Volume Pricing	5 In Stock
4mm Dia. x 101mm Length, 0.6% Dopant, Nd:YAG Laser Rod	#17-626	£569.08 Volume Pricing	5 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com