

[All Products](#) / [Lights and Illumination](#) / [Machine Vision Lighting](#) / [Spot Lights](#)

Advanced Illumination MicroBrite High Intensity Spot Lights

See More by [Advanced Illumination](#)



- High Intensity Output up to 60,000 Lux
- Rectangular Format Spot Light for Off-Axis Applications
- [MicroBrite Compact Spot Lights](#) Also Available
- Optional Manual Intensity Adjustments ([#86-887](#) and [#89-555](#)) Recommended

Common Specifications

General			
Type of Illumination:	LED Illuminator	Note:	Optional Manual Intensity Adjustment #86-887 and #89-555 are Available
Manufacturer:	Advanced Illumination	Geometry:	Spot Light
Illumination Mode:	Constant		
Physical & Mechanical Properties			
Dimensions (mm):	44.5 x 32.2 x 20.1		
Weight (g):	168		
Hardware & Interface Connectivity			
Connector:	Flying Leads		
Power Supply:	Power Supply Required and Sold Separately: USA: #66-855 Europe: #66-855 Japan: #89-513 Korea: #33-773 China: #66-855	Length of Cable (m):	2
Environmental & Durability Factors			
Operating Temperature (°C):	0 - 60		

Technical Information

Products

Dimensions (mm)	Color	Wavelength (nm)	Stock Number	Price	Buy
44.5 x 32.2 x 20.1	White	-	#18-588	£416.50	Contact Us
44.5 x 32.2 x 20.1	UV	365.00	#18-593	£476.00	1 In Stock
44.5 x 32.2 x 20.1	Blue	470.00	#18-590	£416.50	1 In Stock
44.5 x 32.2 x 20.1	Green	530.00	#18-591	£416.50	Contact Us
44.5 x 32.2 x 20.1	Red	625.00	#18-589	£416.50	1 In Stock
44.5 x 32.2 x 20.1	IR	850.00	#18-592	£437.75	1 In Stock
44.5 x 32.2 x 20.1	IR	940.00	#18-594	£437.75	1 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com