

[All Products](#) / [Cameras](#) / [Gigabit Ethernet Cameras](#)

IDS Imaging uEye+ FA IP65/67 PoE Cameras [See More by IDS Imaging Development Systems](#)



- Designed for Harsh Environments
- Robust IP65/67 Housing for Dust and Washdown Protection
- Compatible with [TECHSPEC® Cw Series Lenses](#)
- IP65/67 Rated Accessories and Illumination Also Available

Common Specifications

General			
Manufacturer:		IDS Imaging Development Systems	Camera Series: uEye+ FA
Physical & Mechanical Properties			
Dimensions (mm):		41 x 53 x 42.7 (excludes connectors and lens mount)	Housing: Full
Sensor			
Image Buffer:		128MB	Type of Sensor: Progressive Scan CMOS
Machine Vision Standard:		GigE Vision	
Hardware & Interface Connectivity			
Interface:		GigE (PoE)	Power Supply: Power over Ethernet (PoE) or 12 - 24VDC via GPIO with #19-692
Connector:		GigE M12, screwable	
Interface Port Orientation:		Back Panel	
Threading & Mounting			
Mount:		C-Mount	
Mounting Threads:		$\frac{1}{4}$ -20 with Tripod Mount Adapter #19-694	
Environmental & Durability Factors			
Operating Temperature (°C):		0 to +55	
Storage Temperature (°C):		-20 to +60	

Technical Information

Products

Type	Model Number	Sensor Format	Resolution (Megapixels)	Connector	Mount	Stock Number	Price	Buy
Color Camera	GV-5240FA-C-HQ	1/1.8"	1.31	GigE M12, screwable	C-Mount	#26-295	£616.25	Contact Us
Monochrome Camera	GV-5240FA-M-GL	1/1.8"	1.31	GigE M12, screwable	C-Mount	#26-296	£616.25	1 In Stock
Mono NIR	GV-5240FA-NIR-GL	1/1.8"	1.31	GigE M12, screwable	C-Mount	#26-297	£705.50	5 In Stock
Color Camera	GV-5250FA-C-HQ	1/1.8"	1.92	GigE M12, screwable	C-Mount	#26-298	£684.25	1 In Stock
Monochrome Camera	GV-5250FA-M-GL	1/1.8"	1.92	GigE M12, screwable	C-Mount	#26-299	£684.25	1 In Stock
Color Camera	GV-5880FA-C-HQ	1/1.8"	6.41	GigE M12, screwable	C-Mount	#26-313	£569.50	1 In Stock
Monochrome Camera	GV-5880FA-M-GL	1/1.8"	6.41	GigE M12, screwable	C-Mount	#26-314	£569.50	1 In Stock
Color Camera	GV-5800FA-C-HQ	1"	20.44	GigE M12, screwable	C-Mount	#26-309	£790.50	1 In Stock
Monochrome Camera	GV-5800FA-M-GL	1"	20.44	GigE M12, screwable	C-Mount	#26-310	£790.50	1 In Stock
Color Camera	GV-5890FA-C-HQ	1/1.7"	12.00	GigE M12, screwable	C-Mount	#26-315	£616.25	1 In Stock
Monochrome Camera	GV-5890FA-M-GL	1/1.7"	12.00	GigE M12, screwable	C-Mount	#26-316	£616.25	1 In Stock
Color Camera	GV-5040FA-C-HQ	1/2.9"	1.58	GigE M12, screwable	C-Mount	#26-287	£573.75	1 In Stock
Monochrome Camera	GV-5040FA-M-GL	1/2.9"	1.58	GigE M12, screwable	C-Mount	#26-288	£573.75	1 In Stock
Monochrome Camera	GV-5260FA-M-GL	1/1.2"	2.30	GigE M12, screwable	C-Mount	#26-300	£688.50	1 In Stock
Mono POL	GV-5080FA-P-GL	2/3"	5.01	GigE M12, screwable	C-Mount	#26-289	£2,388.50	1 In Stock

Mono POL	GV-5000FA-P-GL	1.1"	12.29	GigE M12, screwable	C-Mount	#26-286	£3,179.00	Contact Us
Color Camera	GV-5280FA-C-HQ	2/3"	5.01	GigE M12, screwable	C-Mount	#26-303	£926.50	1 In Stock
Monochrome Camera	GV-5280FA-M-GL	2/3"	5.01	GigE M12, screwable	C-Mount	#26-304	£926.50	2 In Stock
Color Camera	GV-5270FA-C-HQ	1/1.8"	3.19	GigE M12, screwable	C-Mount	#26-301	£518.50	1 In Stock
Monochrome Camera	GV-5270FA-M-GL	1/1.8"	3.19	GigE M12, screwable	C-Mount	#26-302	£518.50	1 In Stock
Color Camera	GV-5290FA-C-HQ	1"	8.85	GigE M12, screwable	C-Mount	#26-305	£1,491.75	1 In Stock
Monochrome Camera	GV-5290FA-M-GL	1"	8.85	GigE M12, screwable	C-Mount	#26-306	£1,491.75	1 In Stock
Color Camera	GV-5860FA-C-HQ	1/3"	2.12	GigE M12, screwable	C-Mount	#26-311	£607.75	1 In Stock
Monochrome Camera	GV-5860FA-M-GL	1/3"	2.12	GigE M12, screwable	C-Mount	#26-312	£607.75	1 In Stock
Color Camera	GV-5200FA-C-HQ	1.1"	12.29	GigE M12, screwable	C-Mount	#26-293	£1,840.25	1 In Stock
Monochrome Camera	GV-5200FA-M-GL	1.1"	12.29	GigE M12, screwable	C-Mount	#26-294	£1,840.25	1 In Stock
Color Camera	GV-50C0FA-C-HQ	1/2.3"	2.35	GigE M12, screwable	C-Mount	#26-291	£578.00	1 In Stock
Monochrome Camera	GV-50C0FA-M-GL	1/2.3"	2.35	GigE M12, screwable	C-Mount	#26-292	£578.00	1 In Stock
Color Camera	GV-5990FA-C-HQ	1.1"	20.36	GigE M12, screwable	C-Mount	#26-317	£1,908.25	1 In Stock
Monochrome Camera	GV-5990FA-M-GL	1.1"	20.36	GigE M12, screwable	C-Mount	#26-318	£1,908.25	1 In Stock

[#26-308 Clearance](#)



Clearance

Availability
is limited,
so buy
before
these
products
disappear.
Sorry, we
cannot
accept
returns.
Receive
up to 80%
off select
products.

Color Camera	GV- 5580FA- C-HQ	1/2.5"	4.92	GigE M12, screwable	C- Mount	£527.00	1 In Stock
-----------------	------------------------	--------	------	------------------------	-------------	---------	------------

