

[All Products](#) / [Optics](#) / [Optical Filters](#) / [Bandpass Filters](#)

Ultra Narrow Traditional Coated Bandpass Filters



- Bandwidths Between 0.2 and 5.0nm
- OD 4.0 Blocking Between 200 and 1200nm
- Rapid Custom Designs Available
- [Ultra Narrow Hard Coated Bandpass Filters](#) Also Available

Common Specifications

Physical & Mechanical Properties

Diameter (mm):	25.00 +0.00/-0.25	Clear Aperture CA (mm):	21.00
Substrate Thickness (mm):	6 +0.00/-0.25		

Optical Properties

Angle of Incidence (°):	0
Substrate:	Soda Lime Glass & Filter Glass

Technical Information

Products

Dia. (mm)	CWL (nm)	FWHM (nm)	Minimum Transmission (%)	Substrate Thickness (mm)	Stock Number	Price	Buy
25.00	532.00	0.20	>45	6	#21-381	£1,444.58 Volume Pricing	1 In Stock
25.00	632.80	0.20	>45	6	#21-383	£1,444.58 Volume Pricing	2 In Stock
25.00	656.30	0.20	>45	6	#21-384	£1,444.58 Volume Pricing	2 In Stock
25.00	532.00	0.50	>45	6	#21-385	£1,260.72 Volume Pricing	2 In Stock
25.00	632.80	0.50	>45	6	#21-386	£1,260.72 Volume Pricing	4 In Stock
25.00	656.30	0.50	>45	6	#21-387	£1,260.72 Volume Pricing	4 In Stock
25.00	532.00	1.00	>50	6	#21-388	£1,081.24 Volume Pricing	2 In Stock
25.00	632.80	1.00	>55	6	#21-389	£1,081.24 Volume Pricing	2 In Stock
25.00	656.30	1.00	>55	6	#21-390	£1,081.24 Volume Pricing	2 In Stock
25.00	1,064.00	1.00	>50	6	#21-391	£1,352.65 Volume Pricing	1 In Stock
25.00	532.00	2.00	>55	6	#21-392	£1,081.24 Volume Pricing	1 In Stock
25.00	632.80	2.00	>55	6	#21-393	£1,081.24 Volume Pricing	2 In Stock
25.00	656.30	2.00	>55	6	#21-394	£1,081.24 Volume Pricing	1 In Stock
25.00	1,064.00	2.00	>55	6	#21-395	£1,352.65 Volume Pricing	3 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
 Phone: 1-800-363-1992 :
www.edmundoptics.com