

[All Products](#) / [Lights and Illumination](#) / [Machine Vision Lighting](#) / [Flat Dome Lights](#)

## Effilux Flat Dome Lights



- Dome Light Performance in a Flat Housing
- Integrated Analog Controller for Precise Intensity and Dimming
- Anti-Reflection System to Absorb Stray Light
- Continuous or Strobe mode

### Common Specifications

#### General

<b>Type of Illumination:</b>	LED Illuminator	<b>Manufacturer:</b>	Effilux
<b>Geometry:</b>	Flat Dome Light	<b>Illumination Mode:</b>	Constant

#### Hardware & Interface Connectivity

<b>Input Voltage (V):</b>	24	<b>Power Supply:</b>	Power Supply Required and Sold Separately: USA: <a href="#">#15-874</a> Europe: <a href="#">#15-875</a> Japan: <a href="#">#73-409</a> Korea: <a href="#">#73-409</a> China: <a href="#">#15-874</a>
---------------------------	----	----------------------	---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

## Technical Information

## Products

Color	Active Area (mm)	Stock Number	Price	Buy
Red	200 x 200	<a href="#">#22-106</a>	£702.95	Contact Us
Blue	200 x 200	<a href="#">#22-107</a>	£702.95	Contact Us
White	300 x 300	<a href="#">#22-108</a>	£1,200.20	1 In Stock
Red	300 x 300	<a href="#">#22-109</a>	£1,200.20	Contact Us
Blue	300 x 300	<a href="#">#22-110</a>	£1,200.20	Contact Us



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK  
Phone: 1-800-363-1992 :  
[www.edmundoptics.com](http://www.edmundoptics.com)