

[All Products](#) / [Optics](#) / [SCHOTT Optical Components](#)

SCHOTT Calibrated Neutral Density (ND) Filters

See More by [SCHOTT Optical Components](#)



- Calibrated for Specific Wavelengths
- Optical Densities Ranging from 0.3 to 3.0
- NG3, NG4, NG5, NG9, or NG11 Glass Types

Common Specifications

Physical & Mechanical Properties

Dimensions (mm):	50.0 x 50.0 ±0.2	Clear Aperture CA (mm):	48.5 x 48.5
Parallelism (arcmin):	≤3	Edges:	Fine Ground
Bevel:	0.5 x 45°	Shape of Back Surface:	Plano

Optical Properties

Coating:	Uncoated	Surface Quality:	60-40
-----------------	----------	-------------------------	-------

Technical Information

Products

Glass/Filter Number	Optical Density OD (Average)	DWL (nm)	Stock Number	Price	Buy
SCHOTT NG11	0.3	405	#21-366	£150.59 Volume Pricing	2 In Stock
SCHOTT NG5	0.5	405	#21-367	£150.59 Volume Pricing	5 In Stock
SCHOTT NG4	1.0	405	#21-368	£150.59 Volume Pricing	4 In Stock
SCHOTT NG3	2.0	405	#21-369	£150.59 Volume Pricing	4 In Stock
SCHOTT NG3	3.0	405	#21-370	£150.59 Volume Pricing	4 In Stock
SCHOTT NG11	0.3	633	#21-371	£150.59 Volume Pricing	3 In Stock
SCHOTT NG5	0.5	633	#21-372	£150.59 Volume Pricing	5 In Stock
SCHOTT NG4	1.0	633	#21-373	£150.59 Volume Pricing	5 In Stock
SCHOTT NG3	2.0	633	#21-374	£150.59 Volume Pricing	3 In Stock
SCHOTT NG9	3.0	633	#21-375	£150.59 Volume Pricing	5 In Stock
SCHOTT NG11	0.3	785	#21-376	£150.59 Volume Pricing	5 In Stock
SCHOTT NG5	0.5	785	#21-377	£150.59 Volume Pricing	5 In Stock
SCHOTT NG4	1.0	785	#21-378	£150.59 Volume Pricing	3 In Stock
SCHOTT NG9	2.0	785	#21-379	£150.59 Volume Pricing	4 In Stock
SCHOTT NG9	3.0	785	#21-380	£150.59 Volume Pricing	4 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com