

[All Products](#) / [Imaging Lenses](#) / [Fixed Focal Length Lenses](#)

Computar Motorized LensConnect Fixed Focal Length Lenses



- Focus and Iris Controlled via Simple USB Interface
- 12 MegaPixels, 1/1.1", C-Mount
- Focal Lengths Ranging from 8mm – 50mm
- [Variable Focal Length Option](#) Available

Common Specifications

General			
Series:		Computar Motorized LensConnect	
Physical & Mechanical Properties			
Iris Option:		Motorized	
Outer Diameter (mm):		59.5	
Optical Properties			
Maximum Image Circle (mm):		14.00	
Sensor			
Maximum Sensor Format:		1/1.1"	Resolution (Megapixels): 12.00
Pixel Size (µm):		3.45	
Hardware & Interface Connectivity			
Control Interface:		USB2.0 TypeA	
Length of Cable (mm):		300 ±20	
Threading & Mounting			
Mount:		C-Mount	

Technical Information

Products

FL (mm)	Max. Sensor Format	Aperture (f/#)	WD (mm)	Stock Number	Price	Buy
8.00	1/1.1"	f/2.8 - f/16	100 - ∞	#24-189	£1,066.75	2 In Stock
12.00	1/1.1"	f/2.4 - f/16	100 - ∞	#24-190	£1,066.75	1 In Stock
16.00	1/1.1"	f/2.3 - f/16	110 - ∞	#24-191	£1,066.75	1 In Stock
25.00	1/1.1"	f/2.3 - f/16	120 - ∞	#24-192	£1,066.75	2 In Stock
35.00	1/1.1"	f/2.5 - f/16	160 - ∞	#24-193	£1,066.75	1 In Stock
50.00	1/1.1"	f/2.8 - f/16	200 - ∞	#24-194	£1,066.75	1 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com