

[All Products](#) / [Optomechanics](#) / [Motorized Translation Stages](#) / [Motorized Goniometers](#)

Zaber™ Motorized Goniometers See More by [Zaber™](#)



- 40mm and 60mm Center of Rotation Options
- Vacuum-Compatible Options
- Small Footprint with a Low Profile for Compact Systems
- 30N (~3kg) Centered Load Capacity
- Available with Integrated, 200 Counts per Revolution (CPR) Motor Mounted Encoder

Common Specifications

General

Type of Motor: 2-Phase Stepper

Physical & Mechanical Properties

Type of Movement: Goniometer

Guide System: Crossed Roller Bearing

Height (mm): 20.8

Load Capacity (kg): 3

Electrical

Current (mA): 350

Hardware & Interface Connectivity



Type of Drive: Precision Worm Gear

Environmental & Durability Factors

Operating Temperature (°C): 0 to +50

Technical Information

Products

Title	Stock Number	Price	Buy
#74-718 New			
40mm Center of Rotation, High Vacuum (10^{-6} Torr) Motorized Goniometer Stage, Integrated Controller			
	New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	£5,326.95	1 In Stock
#74-721 New			
60mm Center of Rotation, High Vacuum (10^{-6} Torr) Motorized Goniometer Stage, Integrated Controller			
	New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	£5,326.95	1 In Stock
40mm Center of Rotation, Motorized Goniometer Stage, Integrated Controller	#26-075	£2,346.34	1 In Stock
60mm Center of Rotation, Motorized Goniometer Stage, Integrated Controller	#26-076	£2,346.34	1 In Stock
40mm Center of Rotation, Motorized Goniometer Stage, Integrated Controller with Encoder	#26-077	£2,573.97	1 In Stock
60mm Center of Rotation, Motorized Goniometer Stage, Integrated Controller with Encoder	#26-078	£2,573.97	1 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com