

[All Products](#) / [Lasers](#) / [Laser Sources](#) / [Gas Lasers](#)

Lasos Fiber Coupled Helium-Neon (HeNe) Lasers



- 543nm, 594nm, and 633nm Wavelength Options
- Low Noise and High Stability
- Fiber Coupled for Easy System Integration
- Factory Fiber Coupled for Optimal Alignment and Output Power



Common Specifications

General

Type of Laser:	HeNe
----------------	------

Physical & Mechanical Properties

Diameter of Laser Head (mm):	45
------------------------------	----

Optical Properties

Polarization:	$\geq 100:1$	Beam Diameter (mm):	0.73
---------------	--------------	---------------------	------

Electrical

RMS Noise:	25Hz - 1MHz: <1.5%
------------	--------------------

Hardware & Interface Connectivity

Power Supply:	Power Supply Required and Sold Separately: USA: #28-080 Europe: #28-080 Japan: Not Available Korea: Not Available China: Not Available
---------------	---

Technical Information

Products

Title	Stock Number	Price	Buy
0.7mW Linear Polarization, 543nm Green HeNe Laser	#28-073	£4,845.00	Contact Us
1.3mW Linear Polarization, 594nm Yellow HeNe Laser	#28-062	£4,360.50	1 In Stock
3mW Linear Polarization, 632.8nm Red HeNe Laser	#28-056	£3,718.75	Contact Us



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com