

1/4-20 Bumper (Package of 4), Sorbothane Bumpers



Stock #55-244 **10 In Stock**

⊖ 1 ⊕ £38⁰⁰

ADD TO CART

Volume Pricing

Qty 1-2	£38.60 each
Qty 3+	£34.24 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

English **Type:**

1/4-20 **Note:**

Physical & Mechanical Properties

25.40 **Thickness (mm):**

Sorbothane **Construction:**

38.10 **Diameter (mm):**

30-65 / bumper **Load Capacity (lbs):**

Threading & Mounting

12.7 **Thread Length (mm):**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

Product Details

- Absorb and Dissipate Vibration
- Stabilize Equipment up to 152lbs
- English, Metric, or Universal Styles

Sorbothane® Mounts absorb (57% absorption efficiency) and dissipate energy (70% specific damping). The mounts reduce vibration to other components by isolating the vibrations within the material while absorbing multi-directional forces. These hemisphere mounts can stabilize equipment weighing up to 38 pounds (hemisphere mounts), 65 pounds (1/4-20 male bumper mounts), or 29.4 kg (M6 male bumper mounts). Sorbothane® Mounts measure 50mm dia. (top) x 26mm thick. The top side of the hemisphere is tacky, while the other side is felt. 1/4-20 or M6 male bumper mounts measure 38.1mm dia. x 25.4mm thick. The threaded screw measures 12mm long. All models have a hardness durometer value of 70. Each package contains 4 mounts.

;