

0-1", 0.00005", IP65 Digimatic Digital Micrometer, No Output, Friction Thimble

See More by [Mitutoyo](#)



Stock **#78-328** NEW **1 In Stock**

- 1 + £221^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	£221.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

0 - 1 inches

Range:

Friction Thimble	Type:
293-348-32	Model Number:
±0.0005	Accuracy (inches):
Physical & Mechanical Properties	
5E-05	Resolution (inches):
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- IP65 Rated QuantuMike® and Digimatic® Models
- Easy-to-Read Digital Display
- 0-1", 1-2", and 2-3" Range Options

Mitutoyo Digital Micrometers provide high accuracy and precision over several measurement ranges, making them ideal for a wide range of applications. The QuantuMike® and Digimatic® micrometer models feature an easy-to-read digital display to reduce the chance of errors and the QuantuMike® model features a rapid action micrometer that enables measurements to be made several times faster than a standard micrometer. Select models have a built-in SPC data output function allowing seamless integration with computers or printers for efficient data recording and analysis. Mitutoyo Digital Micrometers are designed with a friction thimble or ratchet stop to ensure consistent measuring pressure, improving repeatability. With IP65 protection, these micrometers are resistant to physical deterioration due to routine exposure to water, cutting oil or coolant.