

A black, rectangular LUMENTUM flashlight is shown at an angle. The brand name "LUMENTUM" is printed in white on the side, with a small logo to its left. A yellow label with a black triangle is on the top. The front features a silver-colored lens and a textured grip area.

Stock #61-373 3-4 DAYS

1

£1,032.75

Qty 1+

£1,032.75

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Output Power (mW):
>0.8

Polarization:
Random

Power Stability (%):
±2.5

Dimensions (inches):
2.50 x 2.00 x 7.00

Spatial Mode:

>95% TEM ₀₀
Wavelength (nm): 632.80
Weight (lbs): 1.20
Beam Diameter Tolerance (%): ±3
Power Supply: Power Supply Required and Sold Separately. USA: #11-378 Europe: #35-224 Japan: Not Available Korea: Not Available China: #11-378
Warm-Up Time (minutes): 10.00
Beam Divergence Tolerance (%): ±3
Note: For Use in European Markets that Utilize 220V or Requires a 110V to 220V Inversion
RMS Noise: 30 Hz - 10 MHz 1.0%
Beam Diameter (mm): 0.48
Manufacturer: Lumentum
Output Type: Free Space
Type of Laser: HeNe
Beam Divergence (mrad): 1.7
Laser Class - CDRH: IIIa
Color: Red
Operating Lifetime (hours): 12,000
Input Voltage (V): 220
Model Number: 1507-2
Longitudinal Mode Spacing, Nominal (MHz): 1090
Minimum Output Power, TEM₀₀ (mW): 0.8

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View