

TECHSPEC® 0.08X GoldTL™ Telecentric Lens (Mount Included)



0.06X GoldTL™ Telecentric Lens (Mount Included)



Stock **#17-204** 3-4 DAYS

- 1 +

£5,006.50

ADD TO CART

Qty 1+

£5,006.50

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length excluding Threads (mm):
277.28

Horizontal Field of View, 1/2" Sensor:
77.8mm

Horizontal Field of View, 2/3" Sensor:
107.1mm

Filter Thread:

M154 x 1.50 (Female)
Maximum Diameter (mm): 160.00
Numerical Aperture NA, Object Side: 0.0069
Stock No. of Mounting Clamp: #56-873 , Included
Resolution, Image Space MTF @ f/10: 70.6
Number of Elements (Groups): 10 (6)
Note: GoldTL™
Horizontal Field of View, 1/1.8" Sensor: 87.5mm
Typical Telecentricity @ 588nm (°): <0.0123
Typical Distortion @ 588nm (%): 0.038
Type: Telecentric Lens
Primary Magnification PMAG: 0.08X
Maximum Sensor Format: 2/3"
Working Distance (mm): 170-220
Mount: C-Mount
Aperture (f/#): f/6-f/25
Coating: N/4 MgF ₂
Depth of Field (mm): ± 80mm at f/10 (20% @ 20 lp/mm)
FOV @ Max Sensor Format, H x V (mm): 107.1 x 80.2
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View