

TECHSPEC® 0.18mm, Uncoated, N-BK7 Right Angle Prism



N-BK7 Right Angle Prisms

Stock #66-767 3-4 DAYS

⊖

1

⊕

£105.40

ADD TO CART

Qty 1-5

£105.40

Qty 6+

£94.86

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:

Uncoated

Substrate: ☐

[N-BK7](#)

Surface Quality:

20-10

Type: Right Angle Prism
Dimensional Tolerance (mm): ±0.02
Angle Tolerance (arcmin): ±2
Bevel: Protective bevel as needed
Length of Hypotenuse (mm): 0.30
Length of Legs (mm): 0.18
Image Orientation: Left-Handed
Ray Deviation (°): 90
Wavelength Range (nm): 350 - 2200
Surface Flatness (P-V): λ/4

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View