

0.2 x 40° Diffusing Angle 2" x 2" Unmounted



Stock **#47-999** CLEARANCE 3-4 DAYS

-

1

+

£206.13

ADD TO CART

Qty 1-5
£206.13
Qty 6+
£175.31
Volume Pricing
Request Quote

ⓘ

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle Tolerance (°):
±0.5 x ±4

Diffusing Angle (°):
0.2 x 40 (FWHM)

Dimensional Tolerance (mm):
±0.5

Dimensions (inches):

2 x2
Dimensions (mm): 50.80 x 50.80
Operating Temperature (°C): -30 to +100 (Maximum of 240 Hours)
Substrate: ☐ Polycarbonate
Thickness (mm): 0.78
Transmission (%): >85
Type: Holographic Diffuser
Wavelength Range (nm): 400 - 700
Width (mm): 50.80
Construction: Unmounted
Damage Threshold, By Design: ☐ 0.22 J/cm² @ 1064nm, 10ns (typical)
Length (mm): 50.80

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant