

0.2 x 40° Diffusing Angle 50mm Dia Mounted



Stock **#47-998** CLEARANCE 3-4 DAYS

- 1 + **£218.88**

ADD TO CART

Qty 1-5
£218.88

Qty 6+
£186.15

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle Tolerance (°):
±0.5 x ±4

Diffusing Angle (°):
0.2 x 40 (FWHM)

Clear Aperture CA (mm):
45.7

Diameter (mm):

50.00 ±0.1
Operating Temperature (°C): -30 to +100 (Maximum of 240 Hours)
Substrate: ☐ Polycarbonate
Thickness (mm): 2.60
Transmission (%): >85
Type: Holographic Diffuser
Wavelength Range (nm): 400 - 700
Construction: Mounted
Damage Threshold, By Design: ☐ 0.22 J/cm ² @ 1064nm, 10ns (typical)

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant