

0.22 NA UV/VIS Patchcord 50 Micron Fiber w/ FC Connector



Stock #23-713 3-4 DAYS

- 1 + **£164.05**

ADD TO CART

Qty 1-4
£164.05

Qty 5+
£147.90

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Connector:
FC/PC

Numerical Aperture NA:
0.22

Core Diameter (µm):
50

Wavelength:

UV-VIS
Length (m): 1.5
Operating Temperature (°C): -40 to +100
Type: Patchcord
Jacket Material: PVC MONOCOIL (0.112" OD)
Coating Type: Nylon
Fiber Cable Type: Multimode

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View