

[See all 11 Products in Family](#)

0.25" Travel, 0.001" Grad. Mic. Drive S-Face



Drive Mechanisms

Stock **#87-093** **1 In Stock**

1 £68.⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	£68.80 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

English **Type:**

Mitutoyo **Manufacturer:**

148-206-10 **Model Number:**

Physical & Mechanical Properties

Travel (inches):

0.25

Graduation (inches):

0.001

Stem Diameter (mm):

3.5

Stem/Spindle:

Plain/Spherical

Stem Length (mm):

5

Spindle Diameter (mm):

2

Min. Spindle Length (mm):

6.5

Max. Diameter (mm):

6

Overall Length (mm):

32

Hardware & Interface Connectivity

Type of Drive:

English Micrometer

Regulatory Compliance

RoHS 2015:

[Exempt](#)

Certificate of Conformance:

[View](#)

REACH 241:

[Contains SVHC\(s\)](#)

Product Details

- Micrometer, Fine Screw, Digital and Differential Options Available
- Compatible with our [Ball Bearing Stages](#)

These drive mechanisms add versatility to our selection of [ball bearing stages](#). Four options are available: micrometer (English and Metric), fine screw, digital, and differential.

Please reference individual product descriptions to see which stages are compatible with each drive mechanism.

;