

TECHSPEC® 0.25X - 0.5X VariMagTL™ Telecentric Lens



0.25X - 0.5X VariMagTL™ Telecentric Lens, #88-385

Stock **#88-385** 3-4 DAYS

- 1 + **£2,129.25**

ADD TO CART

Qty 1+
£2,129.25

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length (mm):
177.90

Filter Thread:
M62 x0.75 (Female)

Maximum Diameter (mm):
65.0

Resolution:
75 lp/mm @ >20%

Weight (g):

942
Stock No. of Mounting Clamp: #56-025 Sold Separately
Typical Telecentricity @ 588nm (°): <0.1
Typical Distortion @ 588nm (%): <0.1
Type: Telecentric Lens
Primary Magnification PMAG: 0.25X - 0.5X
Maximum Sensor Format: 2/3"
Working Distance (mm): 100.1 - 145
Mount: C-Mount
Style: Telecentric, Variable Magnification
Aperture (f/#): f/6 - Closed
FOV @ Max Sensor Format, H x V (mm): 35.2 x 26.4 - 17.6 x 13.2
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View