

0.3 OD 25mm Dia, Absorptive ND Filter

See More by [Hoya](#)



Stock **#46-212** 3-4 DAYS

-

1

+

£37.40

ADD TO CART

Qty 1-10
£37.40
Qty 11+
£33.15
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00

Optical Density OD (Average):

0.3 ±0.05
Glass/Filter Number: Hoya ND-50
Substrate: ☐ ND Filter Glass
Coating: Uncoated
Index of Refraction n_d: 1.50
Surface Quality: 80-50
Transformation Temperature (°C): 495
Thickness (mm): 2.50
Thickness Tolerance (mm): ±0.5
Transmission (%): 50.0 (average)
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 400 - 700
Dimensional Tolerance (mm): ±0.1
Parallelism (mm): <0.02

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View