

0.3 OD M34 x 0.50, Machine Vision Absorptive ND Filter



Stock #21-716 3-4 DAYS

- 1 + **£53.13**

ADD TO CART

Qty 1-9
£53.13

Qty 10+
£50.83

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Optical Density OD (Average):
0.3

Clear Aperture CA (mm):
29.00

Filter Thread:
M34 x0.50

Substrate: ☐

ND Filter Glass
Surface Quality: 40-20
Transmission (%): 50.00
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 425 - 675
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View