

0.3 OD M49.0 x 0.75, Mounted Absorptive ND Filter



Stock **#54-729** 3-4 DAYS

-

1

+

£36.55

ADD TO CART

Qty 1-9
£36.55

Qty 10+
£33.57

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Optical Density OD (Average): 0.3
Clear Aperture CA (mm): 45.0
Filter Thread: M49 x0.75
Substrate: ☐

ND Filter Glass
Thickness with Mount (mm): 5.00
Surface Quality: 80-50
Transmission (%): 50
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 400 - 700
Mount Thickness (mm): 3.8 ±0.1
Note: AR Coating: MgF ₂
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Mount Diameter (mm): 51.0 +0/-0.2
Mount Thickness Including Threads (mm): 6.3

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View