

0.5 OD 12.5mm Diameter VUV ND Filter



Stock #20-133 3-4 DAYS

-

1

+

£375.70

ADD TO CART

Qty 1-5
£375.70

Qty 6+
£338.13

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50

Optical Density OD (Average):
0.5 +0.10/-0.05

Substrate: ☐
UV Grade MgF₂

Coating: Metallic Based ND, with Dielectric Over-Coat
Surface Quality: 40-20
Thickness (mm): 2.00 ±0.10
Transmission (%): 30.00
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 120 - 200
Clear Aperture (%): 80.00
Transmitted Wavefront, P-V: λ/4
Parallelism (arcsec): 1

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View