

TECHSPEC®

0.5 OD 50mm Square, Reflective ND Filter



Stock #43-814 CLEARANCE 3-4 DAYS

-

1

+

£61.20

ADD TO CART

Qty 1-5
£61.20
Qty 6+
£48.88
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Dimensions (mm):

50.0 x 50.0

Angle of Incidence (°):

0

Optical Density OD (Average):

0.5

Substrate: Float Glass
Length (mm): 50.00
Coating: Surface 1: Inconel
Reflection (%): 30.00
Surface Quality: 80-50
Thickness (mm): 1.60 Nominal
Transmission (%): 32.00
Type: Neutral Density Filter
Width (mm): 50.00
Blocking Wavelength Range (nm): 400 - 700
Dimensional Tolerance (mm): ±0.5
Clear Aperture (%): 80
Neutrality: ±5% of Optical Density
Note: Optical density values are average over specified blocking wavelength range.
Surface Flatness (P-V): 4 - 6λ

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant