

0.5" Travel, 0.001" Grad. Mic. Drive S-Face



Drive Mechanisms

Stock #33-729 **1 In Stock**

⊖ 1 ⊕ £72.80

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1-9 | £72.80 each |
| Qty 10-24 | £65.52 each |
| Need More? | Request Quote |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

English **Type:**
Mtutoyo **Manufacturer:**

Physical & Mechanical Properties

0.5 **Travel (inches):**

| | |
|-----------------|----------------------------------|
| 0.001 | Graduation (inches): |
| 9.5 | Stem Diameter (mm): |
| Plain/Spherical | Stem/Spindle: |
| 9.5 | Stem Length (mm): |
| 5 | Spindle Diameter (mm): |
| 15.5 | Min. Spindle Length (mm): |
| 13 | Max. Diameter (mm): |
| 62 | Overall Length (mm): |

Hardware & Interface Connectivity

| | |
|--------------------|-----------------------|
| English Micrometer | Type of Drive: |
|--------------------|-----------------------|

Regulatory Compliance

| | |
|----------------------------------|------------------------------------|
| Exempt | RoHS 2015: |
| View | Certificate of Conformance: |
| Contains SVHC(s) | REACH 241: |

Product Details

- Micrometer, Fine Screw, Digital and Differential Options Available
- Compatible with our [Ball Bearing Stages](#)

These drive mechanisms add versatility to our selection of [ball bearing stages](#). Four options are available: micrometer (English and Metric), fine screw, digital, and differential.

Please reference individual product descriptions to see which stages are compatible with each drive mechanism.