

TECHSPEC® 0.5mm Diameter, N-BK7 Half-Ball Lens



TECHSPEC® N-BK7 Half-Ball Lenses

Stock #49-567 **17 In Stock**

⊖ 1 ⊕ £46.⁰⁰

ADD TO CART

Volume Pricing

Qty 1-10	£46.00 each
Qty 11-49	£41.20 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Half-Ball Lens **Type:**

Physical & Mechanical Properties

0.50 **Diameter (mm):**

±0.05 **Center Thickness Tolerance (mm):**

0.25 Radius R (mm):

+0.0/-1.5 Radius Tolerance (μm):

0.25 Thickness (mm):

± 2.5 Diameter Tolerance (μm):

Optical Properties

[N-BK7](#) Substrate:

Uncoated Coating:

350 - 2200 Wavelength Range (nm):

Regulatory Compliance

[Compliant](#) RoHS 2015:

[View](#) Certificate of Conformance:

[Compliant](#) Reach 247:

Product Details

- Fiber Coupling Half-Spheres
- Collimating Lenses

TECHSPEC® N-BK7 Half-Ball Lenses are ideal for applications such as fiber communication, endoscopy, microscopy, optical pick-up devices, and laser measurement systems. Half-ball (hemispherical) lenses can be interchanged with full ball lenses if the physical constraints of an application require a more compact design. These collimating lenses are uncoated, with a wavelength range of 350-2200nm. TECHSPEC® N-BK7 Half-Ball Lenses are offered in diameters ranging from 0.50 to 10.00mm.

Technical Information

