

[See all 8 Products in Family](#)

TECHSPEC[®]

0.5mm Diameter, N-BK7 Half-Ball Lens



TECHSPEC[®] N-BK7 Half-Ball Lenses

Stock **#49-567** 17 In Stock

-

1

+

£46⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	£46.00 each
Qty 11-49	£41.20 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Half-Ball Lens

Type:

Physical & Mechanical Properties

0.50

Diameter (mm):

±0.05

Center Thickness Tolerance (mm):

0.25	Radius R (mm):
+0.0/-1.5	Radius Tolerance (μm):
0.25	Thickness (mm):
±2.5	Diameter Tolerance (μm):

Optical Properties

N-BK7	Substrate: ☐
Uncoated	Coating:
350 - 2200	Wavelength Range (nm):

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

• Fiber Coupling Half-Spheres

• Collimating Lenses

TECHSPEC® N-BK7 Half-Ball Lenses are ideal for applications such as fiber communication, endoscopy, microscopy, optical pick-up devices, and laser measurement systems. Half-ball (hemispherical) lenses can be interchanged with full ball lenses if the physical constraints of an application require a more compact design. These collimating lenses are uncoated, with a wavelength range of 350-2200nm. TECHSPEC® N-BK7 Half-Ball Lenses are offered in diameters ranging from 0.50 to 10.00mm.

Technical Information

