

# 0.5" Travel, Eng Micrometer, Solid-Top Ball Bearing Stage



45mm/1.75" Center drive stages and optional brackets

Stock **#37-932** 3-4 DAYS

⊖ 1 ⊕

£442.85

ADD TO CART

Qty 1+

£442.85

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

**Type of Movement:**  
Linear (X)

**Guide System:**  
Ball Bearing

**Type of Drive:**  
English Micrometer

**Drive Orientation:**  
Center Drive

**Type:**

|                                                                   |
|-------------------------------------------------------------------|
| English                                                           |
| <b>Stage Size (mm):</b><br>44.4 x 44.4                            |
| <b>Travel (inches):</b><br>0.5                                    |
| <b>Construction:</b><br>Aluminium Stage                           |
| <b>Graduation (inches):</b><br>0.001                              |
| <b>Height (inches):</b><br>0.75                                   |
| <b>Height (mm):</b><br>19.1                                       |
| <b>Load Capacity, Normal (lbs):</b><br>25                         |
| <b>Note:</b><br>Solid Top                                         |
| <b>Stage Size (inches):</b><br>1.75 x 1.75                        |
| <b>Straight Line Accuracy (inches):</b><br>0.00008/inch of travel |
| <b>Weight (lbs):</b><br>0.5                                       |
| <b>Thrust Capacity, T<sub>a</sub> (lbs):</b><br>10                |
| <b>Thrust Capacity, T<sub>b</sub> (lbs):</b><br>5                 |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |

---