

TECHSPEC® 0.6 OD 12.5mm Dia UV-NIR ND Filter



UV-NIR Neutral Density Filters

Stock **#19-298** 3-4 DAYS

⊖ 1 ⊕ **£106.25**

ADD TO CART

Qty 1-5

£106.25

Qty 6+

£95.20

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.2

Optical Density OD (Average):
0.6

Substrate: ☐

Fused Silica (Coming 7980)	
Coating:	Metallic Based ND
Surface Quality:	40-20
Thickness (mm):	1.50 ±0.10
Transmission (%):	25.0
Type:	Neutral Density Filter
Blocking Wavelength Range (nm):	190 - 1700
Clear Aperture (%):	80.00
Transmitted Wavefront, P-V:	λ/4
Optical Density Tolerance (%):	±10
Parallelism (arcsec):	<5
Regulatory Compliance	
RoHS:	Compliant
Certificate of Conformance:	View