

0.6 OD M52.0 x 0.75, Mounted Absorptive ND Filter



Stock **#54-736** CLEARANCE 3-4 DAYS

- 1 + **£29.71**

ADD TO CART

Qty 1+

£29.71

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Optical Density OD (Average):
0.6

Clear Aperture CA (mm):
48.0

Filter Thread:
M52 x0.75

Substrate: ☐
ND Filter Glass

Thickness with Mount (mm):
5.00

Surface Quality: 80-50
Transmission (%): 25
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 400 - 700
Mount Thickness (mm): 3.8 ±0.1
Note: AR Coating: MgF ₂
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Mount Diameter (mm): 54.0 +0/-0.2
Mount Thickness Including Threads (mm): 6.3

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View