

0.9 OD M58.0 x 0.75, Mounted Absorptive ND Filter



Stock **#54-743** CLEARANCE 3-4 DAYS

- 1 + **£33.11**

ADD TO CART

Qty 1+
£33.11

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Optical Density OD (Average): 0.9
Clear Aperture CA (mm): 54.0
Filter Thread: M58 x0.75
Substrate: ☐ ND Filter Glass
Thickness with Mount (mm): 5.00

Surface Quality: 80-50
Transmission (%): 12.5
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 400 - 700
Mount Thickness (mm): 3.8 ±0.1
Note: AR Coating: MgF ₂
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Mount Diameter (mm): 60.0 +0/-0.2
Mount Thickness Including Threads (mm): 6.3

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View