

1" Max. Opening, Soft Jaw Pliers



Stock **#73-583** [CONTACT US](#)

-

1

+

£24^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	£24.00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

Physical & Mechanical Properties

25.4 (1")	Tip to Tip Distance, Open (mm):
-----------	---------------------------------

Regulatory Compliance

View	Certificate of Conformance:
----------------------	-----------------------------

Product Details

- Non-Marring Cushioned Tips
- Screw-In Cushioned Tip Design
- Replacement Tips Available

The slip joint design utilized in these pliers is ideal for handling optics, camera-lens assemblies, and other delicate components. Jaw openings range from 1" to 2.75" (dependent on model). Jaws feature screw-in plastic cushions to protect fine knurling and delicate finishes. Tool body is laminated and handles are covered with rolled vinyl to ensure proper grip.

;