

[See all 11 Products in Family](#)

## 1" Travel, 0.001" Grad. Mic. Drive S-Face



Drive Mechanisms

Stock **#33-733** **2 In Stock**

⊖ 1 ⊕ £81<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-9	£81.60 each
Qty 10-24	£73.44 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

#### General

English **Type:**  
Mtutoyo **Manufacturer:**

#### Physical & Mechanical Properties

1 **Travel (inches):**

0.001	<b>Graduation (inches):</b>
10	<b>Stem Diameter (mm):</b>
Plain/Spherical	<b>Stem/Spindle:</b>
15	<b>Stem Length (mm):</b>
6.35	<b>Spindle Diameter (mm):</b>
27	<b>Min. Spindle Length (mm):</b>
18	<b>Max. Diameter (mm):</b>
95.5	<b>Overall Length (mm):</b>

## Hardware & Interface Connectivity

English Micrometer	<b>Type of Drive:</b>
--------------------	-----------------------

## Regulatory Compliance

<a href="#">Exempt</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Contains SVHC(s)</a>	<b>REACH 241:</b>

## Product Details

- Micrometer, Fine Screw, Digital and Differential Options Available
- Compatible with our [Ball Bearing Stages](#)

These drive mechanisms add versatility to our selection of [ball bearing stages](#). Four options are available: micrometer (English and Metric), fine screw, digital, and differential.

Please reference individual product descriptions to see which stages are compatible with each drive mechanism.