

TECHSPEC® 10" Diameter x 100" FL Protected Gold, Parabolic Mirror



Stock **#35-726-566** 3-4 DAYS

- 1 + **£2,143.70**

ADD TO CART

Qty 1-2
£2,143.70
Qty 3+
£1,822.40
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Substrate: ☐ BOROFLOAT®

Focal Length Tolerance (%): ±1.5

Surface Quality: 60-40

Surface Accuracy:

N/8
Diameter (inches): 10.00 +0.06/-0
Diameter (mm): 254.00 +1.5/-0
Effective Focal Length EFL (inches): 100.0
Effective Focal Length EFL (mm): 2,540.00
Radius of Curvature (mm): 5,080.00
Aperture (f/#): f/10
Coating: Protected Gold (700-10000nm)
Coating Specification: R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm
Coating Type: Metal
Back Surface: Ground
Clear Aperture CA (mm): 229
Edge Thickness ET (inches): 1.75
Edge Thickness ET (mm): 44.50
Type: Parabolic Mirror
Wavelength Range (µm): 0.7 - 10
Wavelength Range (nm): 700 - 10000
Damage Threshold, Reference:  0.8 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant