

TECHSPEC® 10" Diameter x 60" FL Uncoated, Parabolic Mirror



Stock #32-274-000 3-4 DAYS

- 1 + **£1,761.20**

ADD TO CART

Qty 1-2
£1,761.20
Qty 3+
£1,496.85
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Substrate:
BOROFLOAT®SUPREMAX®

Focal Length Tolerance (%):
±1.5

Surface Quality:
60-40

Surface Accuracy:

N/8
Diameter (inches): 10.0 +0.06/-0
Diameter (mm): 254.00 +1.5/-0
Effective Focal Length EFL (inches): 60.0
Effective Focal Length EFL (mm): 1,524.00
Radius of Curvature (mm): 3,048.00
Aperture (f/#): f/6
Coating: Uncoated
Coating Type: Uncoated
Back Surface: Ground
Clear Aperture CA (mm): 229
Edge Thickness ET (inches): 1.75
Edge Thickness ET (mm): 44.50
Type: Parabolic Mirror

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View