

## 10 lp/mm, 1" x 3", FS w/ Fluorescent, Ronchi



Stock #57-875 CLEARANCE 2 In Stock

£320.<sup>00</sup>

ADD TO CART

#### Volume Pricing

Qty 1-4	£320.00 each
Qty 5+	£304.40 each
Need More?	<a href="#">Request Quote</a>

**!** Prices shown are exclusive of VAT/local taxes

#### Product Downloads

#### Physical & Mechanical Properties

Length (inches):  
3.00

Pattern Size (mm):  
12.7 x 25.4

Thickness (mm):  
1.10

Width (inches):  
1.00

## Optical Properties

### Coating:

Vacuum Deposited Chrome  
Fluorescent Peak Excitation @ 365 nm; Fluorescent  
Peak Emission @ 550 nm

### Frequency (lp/mm):

10.00

### Substrate:

[Fused Silica](#) with Fluorescent Backing

### Optical Density OD (Average):

3.00

## Regulatory Compliance

### RoHS 2015:

[Compliant](#)

### Certificate of Conformance:

[View](#)

### Reach 240:

[Compliant](#)

## Product Details

- Used for Evaluation of Resolution, Field Distortion, and Parfocal Stability
- Ideal for Reticle and Field Calibration Requirements
- Available on Float Glass, Fused Silica, Fused Silica with Fluorescent Backing, and [Opal](#).

Precision Ronchi Ruling Glass slides are excellent for evaluating resolution, field distortion, and parfocal stability, especially of microscopes. Many different Linepairs Per Millimeter (lp/mm) versions available.