

10 x 10mm UV Fused Silica Ground Glass Optical Diffuser



Stock **#63-223** ☐ In Stock

-

1

+

£42.50

ADD TO CART

Qty 1-10
£42.50
Qty 11+
£34.00
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Dimensions (mm):
10.00 x 10.00

Grit: ☐
220

Substrate: ☐
[Fused Silica](#) (Coming 7980)

Thickness (mm): 1.60
Type: Ground Glass Diffuser
Wavelength Range (nm): 200 - 2200
Width (mm): 10.00
Length (mm): 10.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant