

10 x 60° Diffusing Angle 25mm Dia Mounted



Stock **#48-009** 3-4 DAYS

- 1 + **£153.00**

ADD TO CART

Qty 1-5
£153.00

Qty 6+
£130.05

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle Tolerance (°):
±1 x ±6

Diffusing Angle (°):
10 x 60 (FWHM)

Clear Aperture CA (mm):
21.6

Diameter (mm):

25.00 ±0.1
Operating Temperature (°C): -30 to +100 (Maximum of 240 Hours)
Substrate: ☐ Polycarbonate
Thickness (mm): 2.60
Transmission (%): >85
Type: Holographic Diffuser
Wavelength Range (nm): 400 - 700
Construction: Mounted
Damage Threshold, By Design: ☐ 0.22 J/cm ² @ 1064nm, 10ns (typical)

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant