

100 x 100mm 120 Grit Ground Glass Diffuser



Stock #83-384

3-4 DAYS

-

1

+

£37.82

ADD TO CART

Qty 1-10
£37.82
Qty 11+
£34.85
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Coating:

Uncoated

Dimensional Tolerance (mm):

±0.25

Dimensions (mm):

100.00 x 100.00

Edges:

Cut Edges
Grit: ☐ 120
Substrate: ☐ Float Glass
Thickness (mm): 1.60
Type: Ground Glass Diffuser
Wavelength Range (nm): 350 - 2000
Width (mm): 100.00
Note: Sandblasted on first surface
Length (mm): 100.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant