

100 x 100mm 600 Grit Ground Glass Diffuser



Stock **#38-791** 3-4 DAYS

- 1 + **£37.82**

ADD TO CART

Qty 1-10
£37.82
Qty 11+
£34.85
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Coating: Uncoated
Dimensional Tolerance (mm): ±0.76
Dimensions (mm): 100.00 x 100.00
Edges:

Seamed Edges
Grit: ☐ 600
Substrate: ☐ Float Glass
Thickness (mm): 1.60
Type: Ground Glass Diffuser
Wavelength Range (nm): 350 - 2000
Width (mm): 100.00
Note: Sandblasted on first surface
Length (mm): 100.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant