


[See all 9 Products in Family](#)

100 x 150mm, Red, EuroBrite™ Spot Light

See More by [Advanced Illumination](#)



Red AI EuroBrite Spot Light

Stock **#33-454** **1 In Stock**

⊖ 1 ⊕ £500⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£500.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General

50,000 **Operating Lifetime (hours):**

SL-S100150M625 **Model Number:**

LED Illuminator **Type of Illumination:**

Note:
See Technical Information Tab for Typical Intensity

Manufacturer:
Advanced Illumination

Geometry:
Spot Light

Illumination Mode:
Strobed or Constant

Physical & Mechanical Properties

Dimensions (mm):
150 x 139 x 30

Weight (g):
253.00

Active Area (mm):
100 x 150

Optical Properties

Color:
Red

Wavelength (nm):
625

Electrical

Maximum Input Current:
0.42 - 0.49A

Analog Intensity Control:
10% @ 0.7V, 100% @ 10V

Trigger-to-Pulse Latency:
10µm

Hardware & Interface Connectivity

Connector:
Flying Leads

Input Voltage (V):
24V nominal (min. 22 / max. 28)

Power Supply:
Power Supply Required and Sold Separately.
USA: [#66-855](#)
Europe: [#66-855](#)
Japan: [#89-513](#)
Korea: [#33-773](#)
China: [#66-855](#)

Environmental & Durability Factors

Operating Temperature (°C):
0 - 60

Environmental Rating:
IP67

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 233:
[Contains SVHC\(s\)](#)

Product Details

- Daisy Chain up to Four 100 x 150mm Units
- Requires No Heat Sink
- Available in White, Red, and Blue

Advanced Illumination EuroBrite™ Spot Light illuminators feature on-board smart drivers functional during strobe and continuous operation modes making them ideal for the most demanding performance constraints. Adaptive OverDrive™ allows for power optimization while in strobing mode, and Adaptive Thermal Feedback™ gives operational current control to the user, preventing overheating and eliminating the need for a heat sink. These Advanced Illumination EuroBrite™ Spot Light illuminators feature a ruggedized, sealed enclosure, and are available in white, red, or blue versions. The ability to operate four 100 x 150mm units connected to one another, and an analog dimming control operable in both strobe and continuous modes add to illuminator's customizability.

Note: A 24V power supply is required.

Technical Information

Typical Intensity

Size	50 x 75mm	50 x 75mm	50 x 75mm	100 x 150mm
Working Distance	100mm	300mm	600mm	600mm
Area	79 x 56mm	117 x 99mm	ø198mm	325 x 198mm
Typical Irradiance (W/M ²)	100.0	74	28	147
Typical Illuminance (kLux)	34.0	25	10	49

;